

Perlator® Clinic

Laminar Stream - 1.5 gpm

Flow Restricted Regular Size




flow, stop and go®

Features and Benefits

- ▶ Available in 4 color baskets to quickly monitor scheduled maintenance period replacement.
- ▶ Watercolours® design: Color coding to identify flow rate and stream pattern.
- ▶ Patented construction provides a splash-free, crystal clear (non-aerated) stream.
- ▶ Recommended for use in healthcare facilities to prevent mixing air and water.
- ▶ Integrated anti-liming honeycomb replaces conventional wire mesh screens prone to lime build up.
- ▶ Anti-clogging dome screen filters sediment and particles.
- ▶ Available housing finish: chrome.
- ▶ Laser marked housings with statutory marks.

Certifications

ANSI/NSF®-61-372 (pending)
 ASME A112.18.1M and CSA B125 (pending)
 Meets **CALGreen** requirements
 WaterSense (pending)



Thread & Part Number

Part #	Designation	Thread Size
19 035	Insert only - yellow	
19 027	Short dual thread	15/16"-27 x 55/64"-27
19 335	Insert only - green	
19 327	Short dual thread	15/16"-27 x 55/64"-27
19 235	Insert only - blue	
19 227	Short dual thread	15/16"-27 x 55/64"-27
19 135	Insert only - red	
19 127	Short dual thread	15/16"-27 x 55/64"-27

Other product combinations available.


Packaging:

Inserts *1 pc (bag), 6 pcs (bag), 50 pcs (bag)*
 Reg. short dual thread *1 pc (bag), 50 pcs (bag)*

Color Code

Dome	Ring	Basket
Green	Green	Blue, Yellow, Red, Green


Flow Rate Curve



Dimensions

No	mm	In
A	20.88	.822
B	12.00	.472
C	19.97	.786
D	≈ 13	≈ 1/2

Housings



Technical Data

Materials: Body Acetal
 Washer EPDM

Continuous

Short-term (5 minutes max.)
 Per ASME A112.18.1 testing requirements.



LAM-10

NEOPERL, Inc., Waterbury, CT • Tel: 203-756-8437 • Fax: 203-574-2107 • www.neoperl.com

January 2023 - Information subject to change without notice.